Careline

Ceiling mounted multi-function ward lighting solution













Overview

A complete LED lighting solution for hospital wards consisting of;

- 1. Recessed linear luminaire in innovative angular 'U' shape
- 2. Two bedhead downlights at each end of 'U' for patient activity
- 3. One downlight over foot of the bed with optional integrated emergency

The system is supplied as a complete unit with all products pre-wired and mounted into a 1800mm x 1200mm metal frame Specially designed to comply with Healthcare guidelines LG2 and BS EN12464-1 (1000 lux and Ra90)

Controls and Scenes

Careline is a DALI addressable system and as such can be connected to a standalone room or building-wide Whitecroft Connect system

Supplied with 7 button wall control panel for programming on site with the following 6 scenes:

- 1. Examination 1000 lux
- 2. General nursing care 300 lux
- 3. Patient rest / Daytime 30-40 lux
- 4. Reading 300 lux at top of bed
- 5. Night light 5 lux at end of bed and 0.5 lux on pillow
- 6. Observation 20-40 lux

Each scene can be dimmed to suit the needs of the patient and hospital staff, whether through a bed handset (by others) or a wall-mounted switch panel (supplied with the luminaire)

Optics

• 4000K LED

- Ra 90 for optimum colour rendition during nursing activities
- · Linear 'U' luminaire;
 - · Opal diffuser for uniform light output and wipe clean surface
 - · High output light engines
- Two downlights (bed head);
 - o Patient reading or observation
 - Focused 10° distribution of light
- One downlight (foot of bed);
 - · Circulation and night lighting
 - Set back and angled to increase cut off angle to patient for comfort
 - o Optional 3 hour emergency standard or COMEPS addressable auto test
 - Emergency output = 162 lumens

Body

- · Sheet steel panel finished white
- Nominal 1800 x 1200mm body
- · Recessed mounted into Exposed Tee ceiling
 - o 24mm with ceiling grid overlap
 - o 15mm no grid overlap, mastic seal by installer recommended for best finish
- Uses common components with other Whitecroft products to aid future replacements and upgrades
- Complete with flying lead and marshalling box

Order codes

Careline Recessed (Complete Unit)

				B50			
Order Codes	Standard	3hr Emergency	COME L70 PS em ergenc y	L80	L90		
Ra90, 4000K	CL2YR94K	CL2YR94KEM	CL2YR >100k 94KEP*	90k	42k		
Careline uses 6 DALL addresses plus 1 additional where COMEPS addressable emergency is used							

Careline uses 6 DALI addresses plus 1 additional where COMEPS addressable emergency is used


Options

LED Performance

Colour Temp	RA (CRI)
4000K	>80

^{*} can be wired as Easytest if required

Dimensions



1785 1185 83 110 39.5	L	W	Н	H1	KG
	1785	1185	83	110	39.5

To Specify

Recessed fully integrated, multiple source LED lighting system for individual patient care and rest within a ward. DALI protocol to achieve all lighting performance requirements in LG2 & BSEN12464-1:2011, including 1000 lux and Ra90 for examination/treatment. Linear 'U' shaped LED luminaire delivers a virtually continuous line of light. LED downlights angled towards task to maximise performance – as Whitecroft Lighting CARELINE

Application images







